

Laminated Glass Repair System Case, Truck/Car



Description

Repair system for laminated glass repair in a practical case. With all tools that are required for professional repair of minor to major damage to commercial vehicle and passenger car laminate glass windows. The overpressure and underpressure required for the repair is created by a pressure/vacuum pump. The simple design of the system guarantees a safe, effortless operation. Thanks to the high-quality, extremely low-viscosity repair resin, even the finest cracks are reliably filled. Even stone cracks with fragmentation on the surface or with a heavily soiled impact point can be repaired with this in a first-class manner as a cordless mini drill for drilling out the impact point is included. The seal of the large resin chamber has an internal diameter of 9.5 mm and is suitable for the type of large stone cracks that frequently occur on trucks and buses due to their design. The large resin chamber is also ideal for stone cracks with two impact points that are located close together. It is designed so that it can be used on both flat and steep windows. The 125 mm sucker on the base is securely fastened using the installed vacuum pump with just a few strokes of the pump. The stable light metal arm can be shifted and swiveled so that the resin chamber can be effortlessly and precisely positioned above the impact point.

Properties

- simple to use
- very high standard of quality
- optimizes economical use
- professional repairs

Areas of application

Professional repair system for the repair of minor to major damage to commercial vehicle and passenger car laminate glass windows.

Comment

Scope of delivery: Large resin chamber 3/8", small resin chamber 3/16", connecting hose, pressure/vacuum pump, bracket with sucker for pump, inspection mirror with sucker, UV lamp (8 W, 230 V/50 Hz), cordless mini drill 3.6 V, 230 V mains plug with integrated charger, carbide metal rod, cracker, penlight incl. batteries, 2 repair resin 5 ml, size resin 5 ml, stone crack polish 25 ml, stand magnifier 15x, small parts box with the following contents: 3 injection syringes, 3 tubes, 20 Mylar squares, 10 doctor blades, 5 injector seals 3/8", 5 injector seals 3/16", carbide drill bit conical 1.0 mm, carbide drill bit round 1.0 mm, 12 piece grinding and polishing set, stone crack simulator, operating

instructions

Application

The method is described in detail in the included operating instructions.

Available pack sizes

1 pcs Carton 6265
D

Our information is based on thorough research and may be considered reliable, although not legally binding.